


# Mikro-Vickers keménységmérő: HM-210/220

## Konfiguráció

Kérjük, rendelje meg a AVPAK-20 szoftvert  
11AAC666 és a számítógépet is!



### Single indenter configuration HM-200 A-Type sets

<b>Contains:</b>	<b>810-401D-ASET HM-210A</b>
<b>810-401D</b>	Manual main unit HM-210
<b>11AAC106</b>	10x Objective lens
<b>Standard lens</b>	50x Objective lens
<b>810-420</b>	Manual XY stage 25x25mm

810-016 vise not included



<b>Contains:</b>	<b>810-406D-ASET HM-220A</b>
<b>810-406D</b>	Manual main unit HM-220
<b>11AAC106</b>	10x Objective lens
<b>11AAC108</b>	100x Objective lens
<b>Standard lens</b>	50x Objective lens
<b>810-420</b>	Manual XY stage 25x25mm

810-016 vise not included

### Single indenter configuration HM-200 B-Type sets

<b>Contains:</b>	<b>810-404D-BSET1 HM-210B</b>
<b>810-404D</b>	System main unit HM-210
<b>11AAC106</b>	10x Objective lens
<b>Standard lens</b>	50x Objective lens
<b>810-420</b>	Manual XY stage 25x25mm

810-016 vise not included



<b>Contains:</b>	<b>810-409D-BSET1 HM-220B</b>
<b>810-409D</b>	System main unit HM-220
<b>11AAC106</b>	10x Objective lens
<b>11AAC108</b>	100x Objective lens
<b>Standard lens</b>	50x Objective lens
<b>810-420</b>	Manual XY stage 25x25mm

810-016 vise not included

### Double indenter configuration HM-200 B-Type sets

<b>Contains:</b>	<b>810-404D-BSET2 HM-210B</b>
<b>810-404D</b>	System main unit HM-210
<b>11AAC109</b>	Second indenter shaft unit for Knoop test
<b>11AAC106</b>	10x Objective lens
<b>Standard lens</b>	50x Objective lens
<b>810-420</b>	Manual XY stage 25x25mm

810-016 vise not included



<b>Contains:</b>	<b>810-409D-BSET2 HM-220B</b>
<b>810-409D</b>	System main unit HM-220
<b>11AAC110</b>	Second indenter shaft unit for Knoop test
<b>11AAC106</b>	10x Objective lens
<b>11AAC108</b>	100x Objective lens
<b>Standard lens</b>	50x Objective lens
<b>810-420</b>	Manual XY stage 25x25mm

810-016 vise not included

### Single indenter configuration HM-200 C-Type sets

<b>Contains:</b>	<b>810-404D-CSET HM-210C</b>
<b>810-404D</b>	System main unit HM-210
<b>11AAC104</b>	2x Objective lens
<b>11AAC106</b>	10x Objective lens
<b>Standard lens</b>	50x Objective lens
<b>810-462D</b>	Motorized XY stage 100x100mm

810-016 vise not included



<b>Contains:</b>	<b>810-409D-CSET HM-220C</b>
<b>810-409D</b>	System main unit HM-220
<b>11AAC104</b>	2x Objective lens
<b>11AAC106</b>	10x Objective lens
<b>11AAC108</b>	100x Objective lens
<b>Standard lens</b>	50x Objective lens
<b>810-462D</b>	Motorized XY stage 100x100mm

810-016 vise not included

### Single indenter configuration HM-200 D-Type sets

<b>Contains:</b>	<b>810-404D-DSET HM-210D</b>
<b>810-404D</b>	System main unit HM-210
<b>11AAC104</b>	2x Objective lens
<b>11AAC106</b>	10x Objective lens
<b>Standard lens</b>	50x Objective lens
<b>810-462D</b>	Motorized XY stage 100x100mm
<b>810-465</b>	Autofocus unit

810-016 vise not included



<b>Contains:</b>	<b>810-409D-DSET HM-220D</b>
<b>810-409D</b>	System main unit HM-220
<b>11AAC104</b>	2x Objective lens
<b>11AAC106</b>	10x Objective lens
<b>11AAC108</b>	100x Objective lens
<b>Standard lens</b>	50x Objective lens
<b>810-462D</b>	Motorized XY stage 100x100mm
<b>810-465</b>	Autofocus unit

810-016 vise not included